

BRY330C6W Cut Sheet



Bryant watertight pin and sleeve connector, 30A, 250 VAC, 1-phase, 2-pole, 3-wire, 6 hour, accepts cord size 0.565-0.93in, IP67, nylon housing, blue.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY330C6W>

Technical Specifications

Brand	Bryant
Item	Connector
Application	Watertight
Wiring Device Type	Pin and sleeve
With Cap	No
Amperage Rating	30A
Voltage Rating	250 VAC
Number of Phases	1
Number of Poles	2

Number of Wires	3
Wire Size	10-8 AWG
Configuration	6 hour
Cord Diameter	0.565-0.93in
IP Rating	IP67
Housing Material	Nylon
Color	Blue
Manufacturer Part Number	C330C6WA

Agency Approvals

UL Listed File #	E146033
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY330C6W.pdf>
See store item page for other formats.