

BRY330R4W Cut Sheet



Bryant watertight single pin and sleeve receptacle, 30A, 125 VAC, 1-phase, 2-pole, 3-wire, 4 hour, IP67, nylon housing, yellow.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY330R4W>

Technical Specifications

Brand	Bryant
Item	Receptacle
Application	Watertight
Receptacle Type	Single
Wiring Device Type	Pin and sleeve
With Cap	No
Amperage Rating	30A
Voltage Rating	125 VAC
Number of Phases	1

Number of Poles	2
Number of Wires	3
Wire Size	10-8 AWG
Configuration	4 hour
IP Rating	IP67
Housing Material	Nylon
Color	Yellow
Manufacturer Part Number	C330R4WA

Agency Approvals

UL Listed File #	E146032
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY330R4W.pdf>
See store item page for other formats.