

# BRY360C6W Cut Sheet



Bryant watertight pin and sleeve connector, 60A, 250 VAC, 1-phase, 2-pole, 3-wire, 6 hour, accepts cord size 0.97-1.45in, IP67, nylon housing, blue.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY360C6W>

## Technical Specifications

|                           |                |
|---------------------------|----------------|
| <b>Brand</b>              | Bryant         |
| <b>Item</b>               | Connector      |
| <b>Application</b>        | Watertight     |
| <b>Wiring Device Type</b> | Pin and sleeve |
| <b>With Cap</b>           | No             |
| <b>Amperage Rating</b>    | 60A            |
| <b>Voltage Rating</b>     | 250 VAC        |
| <b>Number of Phases</b>   | 1              |
| <b>Number of Poles</b>    | 2              |

|                                 |             |
|---------------------------------|-------------|
| <b>Number of Wires</b>          | 3           |
| <b>Wire Size</b>                | 6-4 AWG     |
| <b>Configuration</b>            | 6 hour      |
| <b>Cord Diameter</b>            | 0.97-1.45in |
| <b>IP Rating</b>                | IP67        |
| <b>Housing Material</b>         | Nylon       |
| <b>Color</b>                    | Blue        |
| <b>Manufacturer Part Number</b> | C360C6WA    |

## Agency Approvals

|                         |  |
|-------------------------|--|
| <b>UL Listed File #</b> | E146033                                |
| <b>CE</b>               | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>       | N/A                                    |
| <b>RoHS Status</b>      | Yes (See CE Doc)                       |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BRY360C6W.pdf>  
See store item page for other formats.