

BRY420C7W Cut Sheet



Bryant watertight pin and sleeve connector, 20A, 480 VAC, 3-phase, 3-pole, 4-wire, 7 hour, accepts cord size 0.41-0.65in, IP67, nylon housing, red.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY420C7W>

Technical Specifications

Brand	Bryant
Item	Connector
Application	Watertight
Wiring Device Type	Pin and sleeve
With Cap	No
Amperage Rating	20A
Voltage Rating	480 VAC
Number of Phases	3
Number of Poles	3

Number of Wires	4
Wire Size	14-12 AWG
Configuration	7 hour
Cord Diameter	0.41-0.65in
IP Rating	IP67
Housing Material	Nylon
Color	Red
Manufacturer Part Number	C420C7WA

Agency Approvals

UL Listed File #	E146033
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY420C7W.pdf>
See store item page for other formats.