

# BRY420P9W Cut Sheet



Bryant watertight pin and sleeve plug, 20A, 250 VAC, 3-phase, 3-pole, 4-wire, 9 hour, accepts cord size 0.41-0.65in, IP67, nylon housing, blue.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY420P9W>

## Technical Specifications

<b>Brand</b>	Bryant
<b>Item</b>	Plug
<b>Application</b>	Watertight
<b>Wiring Device Type</b>	Pin and sleeve
<b>With Cap</b>	No
<b>Amperage Rating</b>	20A
<b>Voltage Rating</b>	250 VAC
<b>Number of Phases</b>	3
<b>Number of Poles</b>	3

<b>Number of Wires</b>	4
<b>Wire Size</b>	14-12 AWG
<b>Configuration</b>	9 hour
<b>Cord Diameter</b>	0.41-0.65in
<b>IP Rating</b>	IP67
<b>Housing Material</b>	Nylon
<b>Color</b>	Blue
<b>Manufacturer Part Number</b>	C420P9WA

## Agency Approvals

<b>UL Listed File #</b>	E146033
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BRY420P9W.pdf>  
See store item page for other formats.