

BRY460C5W Cut Sheet



Bryant watertight pin and sleeve connector, 60A, 600 VAC, 3-phase, 3-pole, 4-wire, 5 hour, accepts cord size 1.05-1.45in, IP67, nylon housing, black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY460C5W>

Technical Specifications

| | |
|---------------------------|----------------|
| Brand | Bryant |
| Item | Connector |
| Application | Watertight |
| Wiring Device Type | Pin and sleeve |
| With Cap | No |
| Amperage Rating | 60A |
| Voltage Rating | 600 VAC |
| Number of Phases | 3 |
| Number of Poles | 3 |

| | |
|---------------------------------|-------------|
| Number of Wires | 4 |
| Wire Size | 6-4 AWG |
| Configuration | 5 hour |
| Cord Diameter | 1.05-1.45in |
| IP Rating | IP67 |
| Housing Material | Nylon |
| Color | Black |
| Manufacturer Part Number | C460C5WA |

Agency Approvals

| | |
|-------------------------|--|
| UL Listed File # | E146033 |
| CE | View CE declarations |
| CSA File # | N/A |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY460C5W.pdf>
See store item page for other formats.