

# BRY460MI12W Cut Sheet



Bryant pin and sleeve mechanical interlock, rotary, enclosed, load break capable, 120/240 VAC, 60A, 1-phase, 3-pole, 4-wire, 12 hour pin and sleeve receptacle, 10kA SCCR, 11.9in x6.9in x8.6in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY460MI12W>

## Technical Specifications

|                           |                                     |
|---------------------------|-------------------------------------|
| <b>Brand</b>              | Bryant                              |
| <b>Item</b>               | Pin and sleeve mechanical interlock |
| <b>Handle Type</b>        | Rotary                              |
| <b>Body Type</b>          | Enclosed                            |
| <b>Fusible</b>            | No                                  |
| <b>Load Break Capable</b> | Yes                                 |
| <b>Number of Poles</b>    | 3                                   |
| <b>Voltage Rating</b>     | 600 VAC                             |
| <b>Amperage Rating</b>    | 60A                                 |

|                               |  |
|-------------------------------|--|
| <b>SCCR Rating</b>            | 10kA SCCR  |
| <b>Connection</b>             | 1-phase, 3-pole, 4-wire, 12 hour pin and sleeve receptacle |
| <b>Mounting</b>               | Wall   |
| <b>UL Rating</b>              | UL 508 rated   |
| <b>Housing Size</b>           | 11.9in x6.9in x8.6in                                       |
| <b>Includes</b>               | Watertight conduit hub and grounding plate                 |
| <b>Additional Information</b> | Lockout/tagout capable. Suitable as motor disconnect       |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E70402                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 033196_C_00                            |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BRY460MI12W.pdf>  
See store item page for other formats.