

BRY460P7W Cut Sheet



Bryant watertight pin and sleeve plug, 60A, 480 VAC, 3-phase, 3-pole, 4-wire, 7 hour, accepts cord size 1.05-1.45in, IP67, nylon housing, red.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY460P7W>

Technical Specifications

Brand	Bryant
Item	Plug
Application	Watertight
Wiring Device Type	Pin and sleeve
With Cap	No
Amperage Rating	60A
Voltage Rating	480 VAC
Number of Phases	3
Number of Poles	3

Number of Wires	4
Wire Size	6-4 AWG
Configuration	7 hour
Cord Diameter	1.05-1.45in
IP Rating	IP67
Housing Material	Nylon
Color	Red
Manufacturer Part Number	C460P7WA

Agency Approvals

UL Listed File #	E146033
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY460P7W.pdf>
See store item page for other formats.