

BRY460R5W Cut Sheet



Bryant watertight single pin and sleeve receptacle, 60A, 600 VAC, 3-phase, 3-pole, 4-wire, 5 hour, IP67, nylon housing, black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY460R5W>

Technical Specifications

Brand	Bryant
Item	Receptacle
Application	Watertight
Receptacle Type	Single
Wiring Device Type	Pin and sleeve
With Cap	No
Amperage Rating	60A
Voltage Rating	600 VAC
Number of Phases	3

Number of Poles	3
Number of Wires	4
Wire Size	6-4 AWG
Configuration	5 hour
IP Rating	IP67
Housing Material	Nylon
Color	Black
Manufacturer Part Number	C460R5WA

Agency Approvals

UL Listed File #	E146032
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY460R5W.pdf>
See store item page for other formats.