

BRY5262GRY Cut Sheet



Bryant industrial heavy duty duplex straight blade receptacle, 15A, 125 VAC, 1-phase, 2-pole, 3-wire, NEMA 5-15, nylon molded housing, gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY5262GRY>

Technical Specifications

Brand	Bryant
Item	Receptacle
Application	Industrial heavy duty
Receptacle Type	Duplex
Blade Type	Straight
With Cap	No
Self-grounding	Yes
Amperage Rating	15A
Voltage Rating	125 VAC

Number of Phases	1
Number of Poles	2
Number of Wires	3
Wire Size	14-10 AWG
Copper Wire Only	Yes
Configuration	NEMA 5-15
Housing Material	Nylon molded
Color	Gray

Agency Approvals

UL Listed File #	E2258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	016215
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BRY5262GRY.pdf>
See store item page for other formats.