

# BRY530MI7W Cut Sheet



Bryant pin and sleeve mechanical interlock, rotary, enclosed, load break capable, 480Y/277 VAC, 30A, 3-phase, 4-pole, 5-wire, 7 hour pin and sleeve receptacle, 10kA SCCR, 10.1in x6.9in x7.8in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY530MI7W>

## Technical Specifications

<b>Brand</b>	Bryant
<b>Item</b>	Pin and sleeve mechanical interlock
<b>Handle Type</b>	Rotary
<b>Body Type</b>	Enclosed
<b>Fusible</b>	No
<b>Load Break Capable</b>	Yes
<b>Number of Poles</b>	3
<b>Voltage Rating</b>	600 VAC
<b>Amperage Rating</b>	30A

<b>SCCR Rating</b>	10kA SCCR
<b>Connection</b>	3-phase, 4-pole, 5-wire, 7 hour pin and sleeve receptacle
<b>Mounting</b>	Wall
<b>UL Rating</b>	UL 508 rated
<b>Housing Size</b>	10.1in x6.9in x7.8in
<b>Includes</b>	Watertight conduit hub and grounding plate
<b>Additional Information</b>	Lockout/tagout capable. Suitable as motor disconnect

## Agency Approvals

<b>UL Listed File #</b>	E70402
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	033196_C_00
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BRY530MI7W.pdf>  
See store item page for other formats.