

BRY560C9W Cut Sheet



Bryant watertight pin and sleeve connector, 60A, 120/208 VAC, 3-phase, 4-pole, 5-wire, 9 hour, accepts cord size 1.18-1.45in, IP67, nylon housing, blue.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY560C9W>

Technical Specifications

Brand	Bryant
Item	Connector
Application	Watertight
Wiring Device Type	Pin and sleeve
With Cap	No
Amperage Rating	60A
Voltage Rating	120/208 VAC
Number of Phases	3
Number of Poles	4

Number of Wires	5
Wire Size	6-4 AWG
Configuration	9 hour
Cord Diameter	1.18-1.45in
IP Rating	IP67
Housing Material	Nylon
Color	Blue
Manufacturer Part Number	C560C9WA

Agency Approvals

UL Listed File #	E146033
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY560C9W.pdf>
See store item page for other formats.