

BW800RAGU-3P700SB Cut Sheet



Fuji Electric molded case circuit breaker, 800A frame, 700A, 480 VAC / 250 VDC, 3-pole, characteristics, thermal magnetic, 50kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BW800RAGU-3P700SB>

Technical Specifications

Brand	Fuji Electric
Item	Circuit breaker
Circuit Breaker Type	Molded case
Circuit Type	Feeder and branch
Current-Limiting	No
Frame Size	800A frame
Amperage Rating	700A
Voltage Rating	480 VAC / 250 VDC
Number of Poles	3

Trip Curve	Characteristics
Trip Type	Thermal magnetic
Interrupting Rating	50kA @ 480 VAC
UL Rating	UL 489 listed
Mounting	Panel
HACR Rated	No
Reverse Feed Capable	Yes
Includes	Line and load lug terminals

Agency Approvals

UL Listed File #	E90584
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BW800RAGU-3P700SB.pdf>
See store item page for other formats.