

BX-04DA-3 Cut Sheet



BRX analog output module, 4-channel, current/voltage, 15-bit and 16-bit. Requires BX-RTB05, BX-RTB05-1 or BX-RTB05-2 terminal block kit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-04DA-3>

Technical Specifications

Brand	BRX
Item	Output module
I/O Module Type	Analog
Number Of Output Channels	4
Output Signal Type	Current/voltage
Analog Output Type	Sinking/sourcing
Isolated Channels	No
Number of Non-Isolated Output Commons	1

Output Resolution	15-bit and 16-bit
Output Current Signal Range	0-20 mA, +/- 20 mA and 4-20 mA
Output Voltage Signal Range	0-5 VDC, 0-10 VDC, +/- 5 VDC and +/- 10 VDC
Requires	BX-RTB05, BX-RTB05-1 or BX-RTB05-2 terminal block kit
Programming Software	Do-more Designer programming software v2.7 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-04DA-3.pdf>
See store item page for other formats.