

BX-05TRS Cut Sheet



BRX relay output module, 5-point, 12-48 VDC/24-240 VAC, (5) Form C, 5 isolated common(s), 1 point(s) per common, 2A/point. Requires BX-RTB08, BX-RTB08-1 or BX-RTB08-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-05TRS>

Technical Specifications

Brand	BRX
Item	Output module
I/O Module Type	Relay
Number of Output Points	5
Nominal Output Voltage	12-48 VDC/24-240 VAC
Relay Configuration	(5) Form C (SPDT) relays
Number of Isolated Commons	5
Jumper Selectable Isolation	No

Number of Points per Common	1
Load Current	2A/point
Fuse Type	User-supplied external fuse
Requires	BX-RTB08, BX-RTB08-1 or BX-RTB08-2 terminal block kit or ZIPLink pre-wired cables
Programming Software	Do-more Designer programming software v2.0 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-05TRS.pdf>
See store item page for other formats.