

BX-16CF3F2 Cut Sheet



BRX discrete combo module, Input: 8-point, 2-5 VDC, sinking/sourcing/TTL, Output: 8-point, 2-5 VDC, sourcing/TTL, 20 mA/point. Requires BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-16CF3F2>

Technical Specifications

| | |
|---|---|
| Brand | BRX |
| Item | Combo module |
| I/O Module Type | Discrete |
| Number of Input Points | 8 |
| Nominal Input Voltage | 2-5 VDC |
| Discrete Input Type | Sinking/sourcing/TTL |
| Number of Non-Isolated Discrete Input Commons | 2 |
| Number of Output Points | 8 |
| Nominal Output Voltage | 2-5 VDC |
| Discrete Output Type | Sourcing/TTL |
| Number of Non-Isolated Discrete Output Commons | 2 |
| Load Current | 20 mA/point |
| Fuse Type | User-supplied external fuse |
| Requires | BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables |
| Programming Software | Do-more Designer programming software v2.8 or later |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E185989 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |