

# BX-16NF3 Cut Sheet



BRX discrete input module, 16-point, 2-5 VDC, sinking/sourcing/TTL, 4 isolated common(s), 4 point(s) per common. Requires BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-16NF3>

## Technical Specifications

<b>Brand</b>	BRX
<b>Item</b>	Input module
<b>I/O Module Type</b>	Discrete
<b>Number of Input Points</b>	16
<b>Nominal Input Voltage</b>	2-5 VDC
<b>Discrete Input Type</b>	Sinking/sourcing/TTL
<b>Fast Response</b>	No
<b>Number of Isolated Input Commons</b>	4
<b>Number of Points per Common</b>	4
<b>Requires</b>	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
<b>Programming Software</b>	Do-more Designer programming software v2.8 or later

## Agency Approvals

<b>UL Listed File #</b>	E185989
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BX-16NF3.pdf>  
See store item page for other formats.