

BX-16TD1 Cut Sheet



BRX discrete output module, 16-point, 12-24 VDC, sinking, 4 isolated common(s), 4 point(s) per common, 0.5A/point. Requires BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-16TD1>

Technical Specifications

Brand	BRX
Item	Output module
I/O Module Type	Discrete
Number of Output Points	16
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sinking
Number of Isolated Output Commons	4

Number of Points per Common	4
Load Current	0.5A/point
Fuse Type	User-supplied external fuse
Requires	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
Programming Software	Do-more Designer programming software v2.0 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-16TD1.pdf>
See store item page for other formats.