

# BX-16TD2W Cut Sheet



BRX discrete output module, 16-point, 12-24 VDC, sourcing, 4 isolated common(s), 4 point(s) per common, 2A/point, overcurrent, overload and wire-break protection. Requires BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-16TD2W>

## Technical Specifications

Brand	BRX
Item	Output module
I/O Module Type	Discrete
Number of Output Points	16
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sourcing
Number of Isolated Output Commons	4
Number of Points per Common	4

Load Current	2A/point
Protection Type(s)	<ul style="list-style-type: none"><li>• overcurrent</li><li>• overload</li><li>• wire-break</li></ul>
External Power Requirement	5-36 VDC
Fuse Type	User-supplied external fuse
Requires	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
Programming Software	Do-more Designer programming software v2.11 or later

## Agency Approvals

UL Listed File #	E185989
UL Recognized File #	NA
UL Hazardous File #	NA
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BX-16TD2W.pdf>  
See store item page for other formats.