

BX-P-OPCUA Cut Sheet



BRX communication POM module, OPC-UA, 1 port, (1) Ethernet 10/100Base-T (RJ45) port(s). For use with all BRX MPUs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-P-OPCUA>

Technical Specifications

Brand	BRX
Item	Communication POM module
Number of Ports	1
Communication Port and Connection Type(s)	(1) Ethernet 10/100Base-T (RJ45)
Port Protocol(s)	OPC-UA Server
Port Speed(s)	10/100 Mbps
For Use With	All BRX MPUs
Programming Software	Do-more Designer programming software v2.11 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	NA
UL Hazardous File #	NA
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BX-P-OPCUA.pdf>
See store item page for other formats.