


BX-P-SER2-TERMFC Cut Sheet



BRX communication POM module, Do-more protocol, Modbus RTU and ASCII, 1 port, buffered, (1) RS-232 (5-pin terminal) port(s). For use with all BRX MPUs. BX-RTB05S terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-P-SER2-TERMFC>

Technical Specifications

Brand	BRX
Item	Communication POM module
Number of Ports	1
Buffered Ports	Yes
Communication Port and Connection Type(s)	(1) RS-232 (5-pin terminal)
Port Protocol(s)	<ul style="list-style-type: none">• Do-more protocol• Modbus RTU Slave• ASCII In/out• K-sequence Slave
Port Speed(s)	up to 115.2k baud
For Use With	All BRX MPUs
Includes	BX-RTB05S terminal block
Programming Software	Do-more Designer programming software v2.7 or later
Additional Information	Optional RTS/CTS hardware flow control

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-P-SER2-TERMFC.pdf>
See store item page for other formats.