


# C0-04TRS-10 Cut Sheet



CLICK relay output module, 4-point, 6-24 VDC/6-240 VAC, (4) Form A (SPST) no-suppression, 4 isolated common(s), 1 point(s) per common, 10A/point. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-04TRS-10>

## Technical Specifications

<b>Brand</b>	CLICK
<b>Item</b>	Output module
<b>I/O Module Type</b>	Relay
<b>Number of Output Points</b>	4
<b>Nominal Output Voltage</b>	6-24 VDC/6-240 VAC
<b>Relay Configuration</b>	(4) Form A (SPST) no-suppression relays
<b>Number of Isolated Commons</b>	4
<b>Jumper Selectable Isolation</b>	No

<b>Number of Points per Common</b>	1
<b>Load Current</b>	10A/point
<b>Fuse Type</b>	User-supplied external fuse
<b>Includes</b>	Removable terminal block
<b>Programming Software</b>	CLICK programming software v2.60 or later and CLICK CPU firmware v2.60 or later

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/C0-04TRS-10.pdf>  
See store item page for other formats.