


C0-08CDR Cut Sheet



CLICK discrete combo module, Input: 4-point, 12-24 VDC, sinking/sourcing, Output: 4-point, 6-240 VAC/6-27 VDC, (1) Form A (SPST) relay, 1A/point. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-08CDR>

Technical Specifications

Brand	CLICK
Item	Combo module
I/O Module Type	Discrete
Number of Input Points	4
Nominal Input Voltage	12-24 VDC
Discrete Input Type	Sinking/sourcing
Number of Non-Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	4
Number of Output Points	4

Nominal Output Voltage	6-240 VAC/6-27 VDC
Relay Configuration	(1) Form A (SPST) relay
Number of Non-Isolated Discrete Output Commons	1
Number of Points per Discrete Output Common	4
Load Current	1A/point
Fuse Type	User-supplied external fuse
Includes	Removable terminal block
Programming Software	CLICK programming software v1.40 or later and CLICK CPU firmware v1.40 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C0-08CDR.pdf>
See store item page for other formats.