


# C0-16NE3 Cut Sheet



CLICK discrete input module, 16-point, 24 VAC/VDC, sinking/sourcing, 4 isolated common(s), 4 point(s) per common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-16NE3>

## Technical Specifications

|                                  |   |
|----------------------------------|---|
| Brand                            | CLICK   |
| Item                             | Input module  |
| I/O Module Type                  | Discrete  |
| Number of Input Points           | 16  |
| Nominal Input Voltage            | 24 VAC/VDC  |
| Discrete Input Type              | Sinking/sourcing  |
| Fast Response                    | No  |
| Number of Isolated Input Commons | 4   |
| Number of Points per Common      | 4   |
| Includes                         | Removable terminal block  |
| Programming Software             | CLICK programming software v1.20 or later and CLICK CPU firmware v1.20 or later |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E157382                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/C0-16NE3.pdf>  
See store item page for other formats.