

C0-4AD2DA-2 Cut Sheet



CLICK analog combo module, Input: 4-channel, voltage, 0-10 VDC, Output: 2-channel, voltage, 0-10 VDC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-4AD2DA-2>

Technical Specifications

Brand	CLICK
Item	Combo module
I/O Module Type	Analog
Number of Input Channels	4
Input Signal Type(s)	Voltage
Analog Input Type	Sinking
Input Resolution	13-bit
Input Voltage Signal Range	0-10 VDC
Number of Output Channels	2

Output Signal Type	Voltage
Analog Output Type	Sourcing
Output Resolution	12-bit
Output Voltage Signal Range	0-10 VDC
External Power Requirement	24 VDC
Includes	Removable terminal block
Programming Software	CLICK programming software v1.40 or later and CLICK CPU firmware v1.40 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C0-4AD2DA-2.pdf>
See store item page for other formats.