

# C2-OPCUA Cut Sheet



CLICK PLUS communication module, OPC-UA Server and SNTCP Client, 1 port, (1) microB-USB and (1) Ethernet 10/100Base-T (RJ45) port(s). For use with all CLICK PLUS PLCs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C2-OPCUA>

## Technical Specifications

|  |   |
|--|---|
| <b>Brand</b>                                     | CLICK PLUS  |
| <b>Item</b>                                      | Communication module  |
| <b>Number of Ports</b>                           | 1   |
| <b>Buffered Ports</b>                            | No  |
| <b>Communication Port and Connection Type(s)</b> | <ul style="list-style-type: none"><li>• (1) microB-USB</li><li>• (1) Ethernet 10/100Base-T (RJ45)</li></ul> |
| <b>Port Protocol(s)</b>                          | <ul style="list-style-type: none"><li>• OPC-UA Server</li><li>• SNTCP Client</li></ul>                      |
| <b>Port Speed(s)</b>                             | 10/100 Mbps   |
| <b>For Use With</b>                              | All CLICK PLUS PLCs   |
| <b>Programming Software</b>                      | CLICK programming software v3.7 or later and CLICK CPU firmware v3.7 or later                               |
| <b>Additional Information</b>                    | Supports OPC-UA v1.04 server or later   |

## Agency Approvals

|                         |  |
|-------------------------|--|
| <b>UL Listed File #</b> | E157382                                |
| <b>CE</b>               | <a href="#">View CE declarations</a>   |
| <b>RoHS Status</b>      | Yes (See CE Doc)                       |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/C2-OPCUA.pdf>  
See store item page for other formats.