

# C3R12104SC Cut Sheet



Hammond enclosure, NEMA 3R, 12 x 10 x 4in (HxWxD), wall mount, with knockouts, galvanized steel, ANSI 61 gray, powder coat finish, screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3R12104SC>

## Technical Specifications

|                                     |                         |
|-------------------------------------|-------------------------|
| <b>Brand</b>                        | Hammond                 |
| <b>Item</b>                         | Enclosure               |
| <b>Slope Top</b>                    | No                      |
| <b>NEMA Rating</b>                  | 3R                      |
| <b>IP Rating</b>                    | IP24                    |
| <b>Nominal Enclosure Dimensions</b> | 12 x 10 x 4in (HxWxD)   |
| <b>Enclosure Height</b>             | 12.12in                 |
| <b>Enclosure Width</b>              | 10.49in                 |
| <b>Enclosure Depth</b>              | 4.28in                  |
| <b>Mounting</b>                     | Wall                    |
| <b>Integral Mounting Feet</b>       | No                      |
| <b>Integral Mounting Flange</b>     | No                      |
| <b>Dual Access</b>                  | No                      |
| <b>Knockouts</b>                    | Yes                     |
| <b>Material</b>                     | Galvanized steel        |
| <b>Color</b>                        | ANSI 61 gray            |
| <b>Finish</b>                       | Powder coat             |
| <b>Cover Type</b>                   | Screw cover             |
| <b>Padlock Attachment Type</b>      | Padlock hasp and staple |
| <b>Padlockable</b>                  | Yes                     |
| <b>Keylocking</b>                   | No                      |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LL21312                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |