

C3R242410SCNKO Cut Sheet



Hammond enclosure, NEMA 3R, 24 x 24 x 10in (HxWxD), wall mount, galvanized steel, powder coat finish, screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3R242410SCNKO>

Technical Specifications

| | |
|-------------------------------------|-------------------------|
| Brand | Hammond |
| Item | Enclosure |
| Slope Top | No |
| NEMA Rating | 3R |
| IP Rating | IP24 |
| Nominal Enclosure Dimensions | 24 x 24 x 10in (HxWxD) |
| Enclosure Height | 24.17in |
| Enclosure Width | 24.52in |
| Enclosure Depth | 10.32in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Galvanized steel |
| Finish | Powder coat |
| Cover Type | Screw cover |
| Padlock Attachment Type | Padlock hasp and staple |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LL21312 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |