

C3R24248HCR Cut Sheet



Hammond enclosure, NEMA 3R, 24 x 24 x 8in (HxWxD), wall mount, galvanized steel, ANSI 61 gray, powder coat finish, hinged screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3R24248HCR>

Technical Specifications

Brand	Hammond	Integral Mounting Flange	Yes
Item	Enclosure	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Material	Galvanized steel
NEMA Rating	3R	Color	ANSI 61 gray
IP Rating	IP24	Finish	Powder coat
Nominal Enclosure Dimensions	24 x 24 x 8in (HxWxD)	Cover Type	Hinged screw cover
Enclosure Height	24.33in	Hinge Type	Continuous hinge
Enclosure Width	24.31in	Number of Hinges Per Door	1
Enclosure Depth	8.34in	Padlock Attachment Type	Padlock hasp and staple
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL21312
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document