

C4XSC864SS Cut Sheet



Hammond enclosure, NEMA 3/4X/12, 8 x 6 x 4in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C4XSC864SS>

Technical Specifications

| | |
|-------------------------------------|---------------------|
| Brand | Hammond |
| Item | Enclosure |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 3/4X/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 8 x 6 x 4in (HxWxD) |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|---------------------------------|---------------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | 304 stainless steel |
| Finish | #4 brush |
| Cover Type | Screw cover |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/C4XSC864SS.pdf>
See store item page for other formats.