


# CD12M-0D-050-A1-A Cut Sheet



AutomationDirect connection cable, M12 axial female to pigtail, 3-pole, PUR jacket, black, 16.4ft/5m cable length, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CD12M-0D-050-A1-A>

## Technical Specifications

Brand	AutomationDirect
Item	Cable
Cable Type	Connection
Connection 1	M12 axial female
Connection 2	Pigtail
Number of Poles	3
Jacket Material	PUR
Jacket Color	Black
Cable Length	16.4ft/5m
IP Rating	IP67

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	080128_0_000
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/CD12M-0D-050-A1-A.pdf>  
See store item page for other formats.