

CDC-0.7X0.7R1.9N Cut Sheet



Murrplastik MP18 cable drag chain, 0.71in inside height, 0.71in inside width, 1.89in bend radius, inside opening, 1.3in pitch, 3.2ft/1m length, black. Requires CDC-KAZ-0.7X0.7 bracket for mounting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CDC-0.7X0.7R1.9N>

Technical Specifications

Brand	Murrplastik
Series	MP18
Item	Cable drag chain
Inside Height	0.71in
Inside Width	0.71in
Bend Radius	1.89in
Opening	Inside
Pitch	1.3in
Length	3.2ft/1m
Color	Black
Requires	CDC-KAZ-0.7X0.7 bracket for mounting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CDC-0.7X0.7R1.9N.pdf>
See store item page for other formats.