

CH30J2I Cut Sheet



Bussmann modular fuse holder, with indicator, accepts Class J fuses, 30A, 600 VAC/VDC or less, 2-pole, 18-1 AWG copper only, integral pressure plate with separate spade connection, 35mm DIN rail or panel mount. Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CH30J2I>

Technical Specifications

Brand	Bussmann	Number of Poles	2
Item	Fuse holder	Conductor Size	18-1 AWG copper only
Modular	Yes	Conductor Connection Type	Integral pressure plate with separate spade connection
Blown Fuse Indicator	Yes	SCCR Rating	200kA SCCR
Multi-Wire	No	Fuse Connection Type	Clip with reinforced spring
Accepts Fuse Class	Class J	Mounting	35mm DIN rail or panel
Amperage Rating	30A	Quantity per Pack	3
Voltage Rating	600 VAC/VDC or less		

Agency Approvals

UL Listed File #	E14853
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	047235
RoHS Status	No
EU REACH	View EU REACH document
Other	None