

# CK1-00-2H Cut Sheet



AutomationDirect capacitive proximity sensor, tubular, 18mm diameter x 87mm body, polybutylene terephthalate housing, NPN/PNP, N.O./N.C. selectable output, 12mm sensing distance, non-flush, 10 Hz switching frequency, IP65 IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CK1-00-2H>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Capacitive
<b>Shape</b>	Tubular
<b>Housing Size</b>	18mm diameter x 87mm body
<b>Housing Material</b>	Polybutylene terephthalate
<b>Barrel Type</b>	Threaded
<b>Adjustable</b>	Yes
<b>Number of Wires</b>	3
<b>Switching Output</b>	NPN/PNP
<b>Operation Mode</b>	N.O./N.C. selectable output
<b>Sensing Distance</b>	12mm
<b>Mounting Type</b>	Non-flush
<b>IO-Link Compatible</b>	No
<b>Switching Frequency</b>	10 Hz
<b>Operating Voltage</b>	10-36 VDC
<b>IP Rating</b>	IP65 IP67
<b>Connection</b>	4-pin M12 quick-disconnect
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E328811
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None