

CL1109HW Cut Sheet



Stahlin Classic series enclosure, NEMA 1/3/3S/3R/4X/12, 11 x 9 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CL1109HW>

Technical Specifications

Brand	Stahlin	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	No
Series	Classic	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	Fiberglass reinforced polyester
Vented	No	Color	Gray
NEMA Rating	1/3/3S/3R/4X/12	Cover Type	Crowned hinged screw cover
Nominal Enclosure Dimensions	11 x 9 x 6in (HxWxD)	Hinge Type	Concealed hinges
Enclosure Height	11.21in	Number of Hinges Per Door	1
Enclosure Width	9.21in	Shelf	No
Enclosure Depth	6.09in	Padlockable	No
Mounting	Wall	Keylocking	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CL1109HW.pdf>
See store item page for other formats.