

CL1513HPL Cut Sheet



Stahlin Classic series enclosure, NEMA 1/3/3S/3R/4X/12, 15 x 13 x 7in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned single-door, (2) quick-release latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CL1513HPL>

Technical Specifications

Brand	Stahlin	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Series	Classic	Knockouts	No
Subpanel	Purchase subpanel separately	Bottom Gland Plate	No
Slope Top	No	Material	Fiberglass reinforced polyester
3-Piece Assembly	No	Color	Gray
Vented	No	Cover Type	Crowned single-door
NEMA Rating	1/3/3S/3R/4X/12	Hinge Type	Concealed hinges
Nominal Enclosure Dimensions	15 x 13 x 7in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	15.21in	Latch Type	(2) quick-release latches
Enclosure Width	13.21in	Padlock Attachment Type	Padlock hasp and staple
Enclosure Depth	7.09in	Shelf	No
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	E333478
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CL1513HPL.pdf>
See store item page for other formats.