

# CLK3CL-24AG-CD Cut Sheet



Patlite LED light bar, 300mm length, 24 VDC operating voltage, daylight white, bracket mount, (1) 4-pin M12 female and (1) 4-pin M12 male, aluminum body, IP66, IP67 and IP69K. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CLK3CL-24AG-CD>

## Technical Specifications

Brand	Patlite
Item	LED light bar
Length	300mm
Operating Voltage	24 VDC
LED Color	Daylight white
Color Temperature	6500K
Mounting	Bracket
Connection	(1) 4-pin M12 female and (1) 4-pin M12 male
Power Consumption	12.5W
Body Material	Aluminum
IP Rating	IP66, IP67 and IP69K
Includes	Mounting bracket

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E306141
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CLK3CL-24AG-CD.pdf>  
See store item page for other formats.