

CMV-C2X-4X Cut Sheet



NITRA pneumatic modular plate, left supply/exhaust end, Cv=12.4, (2) 3/8in push-to-connect inlet(s), 3/8in female NPT exhaust(s), 5/32in (4mm) push-to-connect pilot(s), anodized aluminum body, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CMV-C2X-4X>

Technical Specifications

Brand	NITRA
Item	Modular plate
Working Fluid	Air or inert gas
Pneumatic Function	Left supply/exhaust end
Flow Coefficient	12.4
Inlet Port	(2) 3/8in push-to-connect
Exhaust Port	3/8in female NPT
Pilot Port	5/32in (4mm) push-to-connect
Body Material	Anodized aluminum
IP Rating	IP65
Electrical Connection	25-pin male D-sub
For Use With	CMV series solenoid valves
Requires	CMV series 25-pin female D-sub control cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CMV-C2X-4X.pdf>
See store item page for other formats.