

CMV-E2X-4X Cut Sheet



NITRA pneumatic EtherNet/IP protocol modular plate, left supply/exhaust end, Cv=12.4, (2) 3/8in push-to-connect tubing inlet(s), 3/8in female NPT exhaust(s), 5/32in (4mm) push-to-connect tubing pilot(s), anodized aluminum body, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CMV-E2X-4X>

Technical Specifications

Brand	NITRA
Item	EtherNet/IP protocol modular plate
Working Fluid	Pneumatic
Pneumatic Function	Left supply/exhaust end
Flow Coefficient	12.4
Inlet Port	(2) 3/8in push-to-connect tubing
Exhaust Port	3/8in female NPT
Pilot Port	5/32in (4mm) push-to-connect tubing
Body Material	Anodized aluminum
IP Rating	IP65
Electrical Connection	(2) 5-pin M12 and (1) 4-pin M8 quick-disconnect
For Use With	CMV series solenoid valves
Requires	4-pin M8 power cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document