

CR950-K302-C298 Cut Sheet



Code barcode scanner, 1D and 2D, imager, corded, RS-232, general duty, 1280 x 960 optical resolution. 6ft RS-232 cable and power supply included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CR950-K302-C298>

Technical Specifications

Brand	Code
Item	Barcode scanner
Form Factor	Handheld
Scanner Capability	1D and 2D
Scanner Type	Imager
Connectivity	Corded
Connection	RS-232
Duty Rating	General duty
Optical Resolution	1280 x 960
Decode Capability	<ul style="list-style-type: none">• 1D: BC412, Codabar, Code 11, Code 32, Code 39, Code 93, Code 128, IATA 2 of 5, Interleaved 2 of 5, GS1 DataBar, Hong Kong 2 of 5, Matrix 2 of 5, MSI Plessey, NEC 2 of 5, Plessey, Straight 2 of 5, Telepen, Trioptic, UPC/EAN/JAN• Stacked 1D: GS1 Composite (CC-A/CC-B/CC-C), MicroPDF, PDF417• 2D: Aztec Code, Data Matrix, Data Matrix Rectangular Extension, Micro QR Code, QR Code, QR Model 1
Field Of View	51 degree horizontal by 39.4 degree vertical
Shock Rating	Multiple drops of 6ft on concrete
IP Rating	IP54
Operating Temperature	-20 to +50 deg C (-4 to 122 deg F)
Includes	6ft RS-232 cable and power supply

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document