

CSG664 Cut Sheet



Hammond enclosure, NEMA 1, 6 x 6 x 4in (HxWxD), wall mount, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CSG664>

Technical Specifications

| | |
|-------------------------------------|---------------------|
| Brand | Hammond |
| Item | Enclosure |
| Slope Top | No |
| NEMA Rating | 1 |
| IP Rating | IP20 |
| Nominal Enclosure Dimensions | 6 x 6 x 4in (HxWxD) |
| Enclosure Height | 6.00in |
| Enclosure Width | 6.00in |
| Enclosure Depth | 4.06in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Galvanized steel |
| Cover Type | Screw cover |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | LR21001 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |