


CSG886 Cut Sheet



Hammond enclosure, NEMA 1, 8 x 8 x 6in (HxWxD), wall mount, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CSG886>

Technical Specifications

| | |
|------------------------------|---------------------|
| Brand | Hammond |
| Item | Enclosure |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 1 |
| IP Rating | IP20 |
| Nominal Enclosure Dimensions | 8 x 8 x 6in (HxWxD) |
| Enclosure Height | 8.00in |
| Enclosure Width | 8.00in |
| Enclosure Depth | 6.06in |

| | |
|--------------------------|------------------|
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Galvanized steel |
| Cover Type | Screw cover |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | LR21001 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CSG886.pdf>
See store item page for other formats.