

CTF-5SFT-0400 Cut Sheet



AcuAMP AC current transformer, solid core, 400A primary, 5A secondary, 1.56in diameter sensing window, 1% accuracy, M4 x 0.7 threaded terminal stud with nut.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTF-5SFT-0400>

Technical Specifications

| | |
|----------------------------------|--|
| Brand | AcuAMP |
| Item | Transformer |
| Transformer Type | Current |
| Voltage Type | AC |
| Body Type | Solid core |
| Primary Current | 400A |
| Secondary Current | 5A |
| Sensing Window | 1.56in diameter |
| Accuracy | 1% |
| Secondary Conductors | #16 AWG minimum |
| Secondary Connection Type | M4 x 0.7 threaded terminal stud with nut |
| Mounting | Panel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E488023 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CTF-5SFT-0400.pdf>
See store item page for other formats.