

CTM-27W-M-PM Cut Sheet



C-more CTM series touch screen industrial display, 27 in color TFT LCD, PCAP multi-touch, widescreen, 1920 x 1080 pixel, FHD, LED backlight, (1) VGA input, (1) HDMI video in and (1) USB B port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTM-27W-M-PM>

Technical Specifications

Brand	C-more
Item	Industrial display
Series	CTM
Touch Screen	Yes
Display Size	27 in
Viewable Size	27 in
Display Type	Color TFT LCD
Widescreen	Yes
Display Maximum Colors	16.7M colors
Display Resolution	1920 x 1080 pixel
Display Video Standard	FHD
Touch Panel Type	PCAP multi-touch
Brightness	240nits
Display Orientation	Landscape/portrait

Backlight Type	LED
External Power Requirement	12 VDC
Environmental Requirements	Indoor use only
IP Rating	IP65
Mounting	Panel or VESA
A/V Port and Connection Type(s)	(1) VGA input (DB15HD female) and (1) HDMI video input
Communication Port and Connection Type(s)	(1) USB B
Includes	(1) barrel terminal block connector
Requires	C-more CTM-27W-BRK brackets for panel mounting
Additional Information	Windows and Linux compatible; anti-fingerprint coating

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CTM-27W-M-PM.pdf>
See store item page for other formats.