

# CWF3S-M2U-CD Cutsheet



Patlite LED light bar, 300mm length, 100-240 VAC operating voltage, on/off switch, daylight white, bracket mount, pigtail, polycarbonate/aluminum body, 9.8ft/3m cable length, IP20. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CWF3S-M2U-CD>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	LED light bar
<b>Length</b>	300mm
<b>Operating Voltage</b>	100-240 VAC
<b>Switch Type</b>	On/off
<b>LED Color</b>	Daylight white
<b>Color Temperature</b>	5700K
<b>Mounting</b>	Bracket
<b>Connection</b>	Pigtail
<b>Power Consumption</b>	5W
<b>Body Material</b>	Polycarbonate/aluminum
<b>Cable Length</b>	9.8ft/3m
<b>IP Rating</b>	IP20
<b>Includes</b>	Mounting bracket

## Agency Approvals

<b>UL Listed File #</b>	E495484
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	NONE
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None