

# CWF6S-M2U-CD Cut Sheet

Patlite LED light bar, 600mm length, 100-240 VAC operating voltage, on/off switch, daylight white, bracket mount, pigtail, polycarbonate/aluminum body, 9.8ft/3m cable length, IP20. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CWF6S-M2U-CD>

## Technical Specifications

Brand	Patlite
Item	LED light bar
Length	600mm
Operating Voltage	100-240 VAC
Switch Type	On/off
LED Color	Daylight white
Color Temperature	5700K
Mounting	Bracket
Connection	Pigtail
Power Consumption	10W
Body Material	Polycarbonate/aluminum
Cable Length	9.8ft/3m
IP Rating	IP20
Includes	Mounting bracket

## Agency Approvals

UL Listed File #	E495484
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	NONE
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>