

# CWK2S-24-CD Cut Sheet



Patlite LED light bar, 200mm length, 24 VDC operating voltage, daylight white, bracket mount, pigtail, aluminum body, 9.8ft/3m cable length, IP66 and IP67. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CWK2S-24-CD>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	LED light bar
<b>Length</b>	200mm
<b>Operating Voltage</b>	24 VDC
<b>LED Color</b>	Daylight white
<b>Color Temperature</b>	6500K
<b>Mounting</b>	Bracket
<b>Connection</b>	Pigtail
<b>Power Consumption</b>	8.6W
<b>Body Material</b>	Aluminum
<b>Cable Length</b>	9.8ft/3m
<b>IP Rating</b>	IP66 and IP67
<b>Includes</b>	Mounting bracket

## Agency Approvals

<b>UL Listed File #</b>	E306141
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	NONE
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>