

CWK6S-24-CD Cut Sheet



Patlite LED light bar, 600mm length, 24 VDC operating voltage, daylight white, bracket mount, pigtail, aluminum body, 9.8ft/3m cable length, IP66 and IP67. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CWK6S-24-CD>

Technical Specifications

Brand	Patlite
Item	LED light bar
Length	600mm
Operating Voltage	24 VDC
LED Color	Daylight white
Color Temperature	6500K
Mounting	Bracket
Connection	Pigtail
Power Consumption	23W
Body Material	Aluminum
Cable Length	9.8ft/3m
IP Rating	IP66 and IP67
Includes	Mounting bracket

Agency Approvals

UL Listed File #	E306141
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CWK6S-24-CD.pdf>
See store item page for other formats.