

# CXE-0N-1A Cut Sheet



AutomationDirect photoelectric sensor, rectangular, plastic housing, through-beam emitter, infrared, 6m sensing distance, 10-36 VDC operating voltage, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CXE-0N-1A>

## Technical Specifications

Brand	AutomationDirect	Number of Wires	3
Item	Photoelectric sensor	Sensing Distance	6m
Shape	Rectangular	Sensitivity	Potentiometer
Housing Size	30 x 15 x 30mm	Switching Frequency	1 kHz
IP Rating	IP65	Light Emission (NP)	Infrared
Housing Material	Plastic	Cable Length	6.5ft/2m
Sensing Method	Through-beam emitter	Connection	Pigtail
Operating Voltage	10-36 VDC	Conductor Size	26 AWG

## Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>