

CXP-AN-1A Cut Sheet



AutomationDirect photoelectric sensor, rectangular, polarized retroreflective, visible red, 2m sensing distance, dark-on, NPN, potentiometer, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CXP-AN-1A>

Technical Specifications

Brand	AutomationDirect	Switching Output	NPN
Item	Photoelectric sensor	Sensing Distance	2m
Shape	Rectangular	Sensitivity	Potentiometer
Housing Size	30 x 15 x 30mm	Operation Mode	Dark-on
IP Rating	IP65	Switching Frequency	1 kHz
Housing Material	Plastic	Light Emission (NP)	Visible red
Sensing Method	Polarized retroreflective	Cable Length	6.5ft/2m
Operating Voltage	10-36 VDC	Connection	Pigtail
Number of Wires	3	Conductor Size	26 AWG

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document